


CVI345 DILATING DISK™ VALVE

Flow Characteristics




% OPEN	C_v	K_v	F_L	X_T
10	9	7.79	0.98	0.52
20	26	22.50	0.93	0.49
30	53	45.80	0.81	0.42
40	9	83.90	0.76	0.36
50	181	156.00	0.71	0.32
60	303	262.00	0.56	0.28
70	515	445.00	0.36	0.24
80	844	731.00	0.23	0.19
90	1220	1060.00	0.17	0.17
100	1345	1160.00	0.14	0.14




What results does the Dilating Disk™ Valve deliver?



Market Comparison How does the Dilating Disk™ Valve compare?



CVI345 DILATING DISK™ VALVE PRESSURE CLASS 150 - 600



A	B	C	D	E	F	G	H	I
ASME B16.5 [NPS]	PRESSURE CLASS [ASME]	FACE TO FACE ISA 75.08 [IN]	CENTERLINE HEIGHT [IN]	DRIVE SQUARE WIDTH [IN]	DRIVE SQUARE HEIGHT [IN]	ISO 5211 YOKE PATTERN [IN]	WEIGHT [LBS]	MAST [IN-LBS]
6"	CL150	17.75	10.827	0.866	0.7	F5 - 1.970 F7 - 2.760 F10 - 4.016	312	8641
	CL300	18.62					361	
	CL600	20.00					443	
8"	CL150	21.38					370	
	CL300	22.38					441	
	CL600	24.00					535	
10"	CL150	26.50					458	
	CL300	27.88					551	
	CL600	32.35					717	
12"	CL150	29.00	542					
	CL300	30.50	665					
	CL600	32.25	819					